

PMI INSUFFLATION TUBING

Designed with the patient's safety in mind to prevent insufflator cross-contamination between patients.



PMI INSUFFLATION TUBING includes high flow, kink-resistant, DEHP-free tubing, with different connector configurations to fit your insufflation needs. Each tubing set is sterile and includes a 0.01 micron filter ensuring a 99.999% efficiency rating.



PMI INSUFFLATION TUBING Features:

- ½ inch tubing, disposable, 10 foot length
- Includes one hydrophobic ULPA 0.01 micron filter
- High flow, 52 liter per minute flow rate
- 4 connection types
- No DEHP-containing plastics were used in device manufacture
- Not manufactured with natural rubber latex
- Sterile, single patient use

PMI INSUFFLATION TUBING Benefits:

- Saves money through standardization
- Simple-to-use with pre-attached connector and filter
- Different connectors fit most popular insufflators
- High flow rates make the insufflation process efficient
- Single use product prevents cross contamination



PMI-10
Swivel Luer



PMI-102
Quick Connector



PMI-1522
15/22mm Connector



PMI-6000
Funnel Connector

Ordering Information:

Item #	Description	Qty.
PMI-10	PMI Insufflation Tubing 10ft, .01 Micron Filter with Swivel Luer Connector	10/box
PMI-102	PMI Insufflation Tubing 10ft, .01 Micron Filter with Quick Connector	10/box
PMI-1522	PMI Insufflation Tubing 10ft, .01 Micron Filter with 15/22mm Connector	10/box
PMI-6000	PMI Insufflation Tubing 10ft, .01 Micron Filter with Funnel Connector	10/box